


ADDITIONAL INFORMATION

ALL OIL PORTS CLOSED PROPERLY AGAINST DUST FOR TRANSPORT AND STORAGE, E.G. WITH PLASTIC CLOSURE CAPS.

| | | | | | | | | | | | | | | | | | |
|----------------------------------|--------------------|--------------|------------------|---------------|--|--------------------------------|------------|---|--|------------------------|--|------------------|--|-------------------|--|------------------|--|
| | | | | | Nicht tol. Maße NON-TOLERANCED DIM. | | | 150 E | | Maßstab SCALE | | 1:2 | | Gewicht WEIGHT | | | |
| Dokumentenart/ DOCUMENT TYPE AGZ | | | | | ±0.3 mm, ±1° | | |  | | Angebots- zeichnung | | OFFER DRAWING | | | | | |
| 7 51 ATEHF 601 | | LL | 12.06.98 | . | Gr.St. | | Datum/DATE | Name/ NAME | Benennung/ TITLE | | | | | | | | |
| 6 Freigaben | | LL | 17.04.98 | . | VOLUME | gez/DWN | 21.11.94 | MG | Hydrozahnradpumpe AZPFF • HYDRAULIC GEAR PUMP AZPFF | | | | | | | | |
| 5 Saugflansch | | mq | 19.11.97 | . | | gez/CHK | . | . | | | | | | | | | |
| 11 51 MAEPE 0395 | | Mu | 15.06.2012 | Wr | | ges/APP | . | . | | | | | | | | | |
| 10 51 ATEMH 1033 | | mq | 09.08.00 | . | Original: DC-MA/EPE | | | Nr./ NO. A 510 245 902 | | | | | | | | | |
| 9 51 ATEMH 1021 | | mq | 01.08.00 | . | DIN A2 | Rexroth Bosch Group | | | | | | | | de/en | | Blatt SHEET 1 | |
| 8 51 ATEMH 776 | | LL | 07.05.99 | . | | | | | | | | | | | | | |
| Nr NO | Änderung CHANGE | gez. DWN. | gültig VAL ID | gepr. CHK. | (MED) | Ers.f./ REPLACES | | | Ers.d./ REPLAC.BY | | | | | | | | |