

## Case lifter EL. Lift = 1300 modular EU



- ▶ Ergonomic parts supply at the workstation
- ▶ Operating mode:  
Manual: Lifting and lowering through hand switch actuation. Suitable for use with Basic and Comfort hand switches  
Automatic: Automatic lifting and lowering.
- ▶ Rollers for semi-mobile use at various workstations
- ▶ New modular floor panel concept: Optionally dowel, front support or side support
- ▶ ESD version for use in ESD-sensitive areas
- ▶ The 10 mm slot enables simple mounting of components from the Basic Mechanic Elements modular system
- ▶ Leveling feet for a floor/level compensation
- ▶ Additional terminal protection
- ▶ Easy start-up; connection via mains cable HD or connecting cable

### Required accessories

- ▶ Basic hand switch or Comfort + hand switch Comfort sensor unit;
- ▶ Mains cable
- ▶ Foot support
- ▶ Attachment bracket

### Recommended accessories

- ▶ Attachment plate
- ▶ Forks
- ▶ Suspension strap

### Ordering information

Product description	Material number
Case lifter EL. Lift=1300 modular EU	3842563303

### Technical data

Permissible load	$F_{\max}$	N	2200
Lifting velocity		mm/s	26
Duty cycle	ED	%	20
Current consumption			max. 16 A
Voltage			100 ... 240 V
Frequency			50 ... 60 Hz
Protection class			IP40 IEC 529

The data specified above only serves to describe the product. Due to the continuing development of our products, no statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not exempt the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.

## Dimensions

