



B 517 232 012	0 517 615 001	AZPS-11-016RNT20MB-S0002	rechts/CW	16	3000	230 *	45.0	93.7	.
B 517 232 011	0 517 615 301	AZPS-12-016LNT20MB-S0002	links/CCW	16	3000	230 *	45.0	93.7	.
B 517 232 094	.	AZPS-12-014LNT20MB-S0002	links/CCW	14	3000	280	45.0	90.3	.
B 517 232 010	0 517 515 002	AZPS-11-014RNT20MB-S0002	rechts/CW	14	3000	280	45.0	90.3	.
B 517 232 009	0 517 515 303	AZPS-11-014LNT20MB-S0002	links/CCW	14	3000	280	45.0	90.3	.
B 517 232 095	0 517 515 312	AZPS-12-011LNT20MB-S0002	links/CCW	11	3500	280	44.5	85.3	.
B 517 232 008	0 517 515 001	AZPS-11-011RNT20MB-S0002	rechts/CW	11	3500	280	44.5	85.3	.
B 517 232 024	0 517 515 302	AZPS-11-011LNT20MB-S0002	links/CCW	11	3500	280	44.5	85.3	.
B 517 232 153	0 517 415 003	AZPS-12-008RNT20PB-S0002	rechts/CW	8	4000	280	40.7	80.3	**, ***
B 517 232 007	0 517 415 001	AZPS-11-008RNT20MB-S0002	rechts/CW	8	4000	280	40.7	80.3	.
B 517 232 006	0 517 415 301	AZPS-11-008LNT20MB-S0002	links/CCW	8	4000	280	40.7	80.3	.
B 517 232 005	0 517 315 001	AZPS-11-005RNT20MB-S0002	rechts/CW	5.5	4000	280	38.6	76.2	.
B 517 232 004	0 517 315 301	AZPS-11-005LNT20MB-S0002	links/CCW	5.5	4000	280	38.6	76.2	.
B 517 232 003	0 517 215 001	AZPS-11-004RNT20MB-S0002	rechts/CW	4	4000	280	37.4	73.7	.
B 517 232 002	0 517 215 301	AZPS-11-004LNT20MB-S0002	links/CCW	4	4000	280	37.4	73.7	.
Entwicklungs Nr.	Bestell-Nr.	Typ-Aufschrift	Dreh- richtung	Volumen [cm ³ /U]	max. Drehzahl [U/min]	max. Druck (intermitt.) [bar]	A Maß [mm]	B	Bemerkungen
DEVELOPMENT NO.	PART NUMBER	DESIGNATION	DIR. OF ROTATION	DISPLACEMENT	MAX. SPEED	MAX. PRESSURE	DIMENSIONS		REMARKS