

SCHALTELEMENT 19"-VARIANTE – 1 SCHALTER + 2 TASTER, 3 SCHLIESSERKONTAKTE, 3 ÖFFNERKONTAKTE

Materialnummer	R961009617
-----------------------	-------------------

Materialkurztext	SCHALTELEMENT TS-EC-E-SST-S3-S3O3
-------------------------	--------------------------------------

- ▶ 1 Schalter mit Rastung, 1 Öffner und 1 Schließer, Betätigung durch Drehen des Schalterknebels;
- 2 Taster mit Federrückstellung, je 1 Öffner und 1 Schließer, Betätigung durch Drücken des Tastknopfes;
- ▶ Alu-Frontplatte mit kratzfester Beschriftung, zur Befestigung in Baugruppenträger in 19"-Technik, berührungsgeschützte 4 mm Laborbuchsen

Höhe	HE	3
Breite	TE	15
Tiefe	mm	36
Gewicht	g	145
Schutzart		IP50
Betriebsspannung (DC)	V	24
Strom max.	A	4



Hydraulics training systems | Components and spare parts

SWITCHING ELEMENT 19" TYPE – 1 SWITCH + 2 PUSH BUTTONS, 3 NO CONTACTS, 3 NC CONTACTS

Material number	R961009617
------------------------	-------------------

Material short text	SCHALTELEMENT TS-EC-E-SST-S3-S3O3
----------------------------	--------------------------------------

- ▶ 1 switch with detent, 1 NC contact and 1 NO contact, operation by turning the switch knob;
- 2 push buttons with spring return, 1 NC contact and 1 NO contact each, operation by pushing the pushbutton;
- ▶ Aluminum front plate with scratch-proof labeling, for fastening in assembly carrier in 19" technology, contact-protected 4 mm laboratory sockets

Height	HE	3
Width	TE	15
Depth	mm	36
Weight	g	145
Protection class		IP50
Operating voltage (DC)	V	24
Max. current	A	4