Cylinder accessories → Cylinder mountings; series CM1

MP4, Rear eye for clevis mounting MP2, AB3

P523_024



00126403_a

Scope of delivery: clevis incl. mounting screws

Part No.	Piston Ø	CD H9	Ø D	Ø D1	E	EW	FL ±0,2	I ±0,5	L 1)	L1 1)	MR 2)
1825805368	16	6	10 H13	4.5	27	12 –0,2/–0,6	16	2.6	10	3	6
1827002300	20	8	12 H13	5.5	34	16 –0,2/–0,6	20	2.6	14	3	8
1827002301	25	8	12 H13	5.5	40	16 –0,2/–0,6	20	2.6	14	3	8
1827001283	32	10	30 H11	6.6	48	26 –0,2/–0,6	22	5.5	12	4.5	10
1827001284	40	12	35 H11	6.6	53	28 –0,2/–0,6	25	5.5	15	4.5	12
1827001285	50	12	40 H11	9	63	32 –0,2/–0,6	27	6.5	15	4.5	12
1827020086	63	16	45 H11	9	73	40 –0,2/–0,6	32	6.5	20	4.5	16
1827001287	80	16	45 H11	11	98	50 –0,2/–0,6	36	10	20	4.5	16
1827001288	100	20	55 H11	11	115	60 –0,2/–0,6	41	10	25	4.5	20
1827004866	125	25	60 H11	14	140	70 –0,5/–1,2	50	10	30	7	26
1827004867	160	30	65 H11	18	180	90 –0,5/–1,2	55	10	35	7	31
1827004868	200	30	75 H11	18	220	90 –0,5/–1,2	60	11	35	7	31
1827004869	250	40	90 H11	22	280	110 –0,5/–1,2	70	11	45	11	41
5239813412	320	45	110 H11	26	350	120 –0,5/–1,2	80	15	50	11	45
R412012202	32	10	30 H11	6.6	48	26 –0,2/–0,6	22	5.5	12	4.5	10
R412012203	40	12	35 H11	6.6	53	28 –0,2/–0,6	25	5.5	15	4.5	12
R412012204	50	12	40 H11	9	63	32 –0,2/–0,6	27	6.5	15	4.5	12
R412012205	63	16	45 H11	9	73	40 –0,2/–0,6	32	6.5	20	4.5	16
R412012206	80	16	45 H11	11	98	50 –0,2/–0,6	36	10	20	4.5	16
R412012207	100	20	55 H11	11	115	60 –0,2/–0,6	41	10	25	4.5	20

Part No.	TG	Material	Surface	Screws	Standardization			
1825805368	18 ±0,2	Die-cast aluminum	-	-	-			
1827002300	22 ±0,4	Steel	galvanized	-	ISO 21287			
1827002301	26 ±0,4	Steel	galvanized	-	ISO 21287			
1827001283	32,5 ±0,2	Aluminum, forged	-	-	ISO 15552			
1827001284	38 ±0,2	Aluminum, forged	-	-	ISO 15552			
1827001285	46,5 ±0,2	Aluminum, forged	-	-	ISO 15552			
1827020086	56,5 ±0,2	Aluminum, forged	-	-	ISO 15552			
1827001287	72 ±0,2	Aluminum, forged	-	-	ISO 15552			

1) Min.
2) Max.

Part numbers marked in bold are available from the central warehouse in Germany, see the shopping basket for more detailed information

Pneumatics catalog, online PDF, as of 2013-02-07, © Bosch Rexroth AG, subject to change

MP4, Rear eye for clevis mounting MP2, AB3

Part No.	TG	Material	Surface	Screws	Standardiza-tion			
1827001288	89 ±0,2	Aluminum, forged	-	-	ISO 15552			
1827004866	110 ±0,3	Aluminum, forged	-	-	ISO 15552			
1827004867	140 ±0,3	Nodular graphite iron	nickel-plated	-	ISO 15552			
1827004868	175 ±0,3	Nodular graphite iron	nickel-plated	-	ISO 15552			
1827004869	220 ±0,3	Nodular graphite iron	nickel-plated	-	ISO 15552			
5239813412	270 ±0,3	Nodular graphite iron	galvanized	-	ISO 15552			
R412012202	32,5 ±0,2	Aluminum	anodized	Stainless steel	ISO 15552			
R412012203	38 ±0,2	Aluminum	anodized	Stainless steel	ISO 15552			
R412012204	46,5 ±0,2	Aluminum	anodized	Stainless steel	ISO 15552			
R412012205	56,5 ±0,2	Aluminum	anodized	Stainless steel	ISO 15552			
R412012206	72 ±0,2	Aluminum	anodized	Stainless steel	ISO 15552			
R412012207	89 ±0,2	Aluminum	anodized	Stainless steel	ISO 15552			

1) Min.
2) Max.