


Cover profiles



- For fixing cables in position
 - To prevent dirt from entering the profile slot
 - Attractive design
 - Soft PVC cover profile for 6 mm slot is provided as a roller
 - Flush with profile
-
- An ESD-conductive connection between the cover profile and the strut profile must be ensured through a design solution, e.g. screw

Product description



Introduction to strut profiles

Ordering codes

	Color	Groove	L (mm)	 ESD	No.
Cover profile, N6 aluminum, anodized	Colorless, natural	6	2000	 1 0	3842523254
Cover profile, soft PVC	Light gray (RAL 7035)	6	10000	1	3842542435
Cover profile, soft PVC	Signal gray (RAL 7004)	6	10000	1	3842555268
Cover profile, N8 aluminum, anodized	Colorless, natural	8	2000	 1 0	3842523256
Cover profile, N8 PP, signal gray	Signal gray (RAL 7004)	8	2000	1	3842548878
Cover profile, N8 PP, black	Black (RAL 9005)	8	2000	 1 0	3842548879
Cover profile, N8 PP, light gray	Light gray (RAL 7035)	8	2000	1	3842548898
Cover profile, N8 PP, red	Red (RAL 3020)	8	2000	1	3842549878
Cover profile, N8 H-PVC, yellow	Yellow (RAL 1023)	8	2000	1	3842518377
Cover profile, N8 PP, yellow	Yellow (RAL 1023)	8	2000	1	3842549879
Cover profile, N8 PP, green	Green (RAL 6032)	8	2000	1	3842549882
Cover profile, N8 H-PVC, blue	Blue (RAL 5010)	8	2000	1	3842538956
Cover profile, N8 PP, blue	Blue (RAL 5010)	8	2000	1	3842549880
Cover profile, N8 H-PVC, orange	Orange (RAL 2004)	8	2000	1	3842538958
Cover profile, N8 PP, orange	Orange (RAL 2004)	8	2000	1	3842549881
Cover profile, N8 H-PVC, colorless	Colorless, transparent	8	2000	1	3842503073

	Color	Groove	L (mm)	 ESD	No.
Cover profile, N8 PET, colorless	Colorless, transparent	8	2000	1	3842549877
Cover profile, N10 aluminum, anodized	Colorless, natural	10	2000	1 0 	3842523258
Cover profile, N10 H-PVC, signal gray	Signal gray (RAL 7004)	10	2000	1	3842548876
Cover profile, N10 H-PVC, black, ESD	Black (RAL 9005)	10	2000	1 0 	3842548877
Cover profile, N10 H-PVC, light gray	Light gray (RAL 7035)	10	2000	1	3842518367
Cover profile, N10 H-PVC, red	Red (RAL 3020)	10	2000	1	3842518368
Cover profile, N10 H-PVC, yellow	Yellow (RAL 1023)	10	2000	1	3842518369
Cover profile, N10 H-PVC, green	Green (RAL 6032)	10	2000	1	3842549888
Cover profile, N10 H-PVC, blue	Blue (RAL 5010)	10	2000	1	3842538955
Cover profile, N10 H-PVC, orange	Orange (RAL 2004)	10	2000	1	3842538957
Cover profile, N10 H-PVC, colorless	Colorless, transparent	10	2000	1	3842191182
Cover profile, N8 PP, green	Green (RAL 6032)	8	2000	1	3842554771