


Bemerkung:

- ① Übersetzungsverhältnis "003" nicht mit Betriebsart "S5-Zyklusbetrieb" lieferbar
 Übersetzungsverhältnis "050" nicht mit Betriebsart "S1-Dauerbetrieb" lieferbar
- ② Abtriebswelle "C" und "D" nicht mit Betriebsart "S1-Dauerbetrieb" lieferbar
- ③ Motor mit Flüssigkeitskühlung
- ④ Motor ohne Flüssigkeitskühlung

Zulässige Kombinationen

Einbaulage Betriebsart	mögliche Übersetzungen		eingeingtes Getriebeumkehrspiel
	1 stufig	2 stufig	
CO	3, 4, 5, 7, 10	20	Nein
MO	4, 5, 7, 10	20, 50	Ja
VO	4, 5, 7, 10	20, 50	Ja

Bildbeispiel: Planetengetriebe



Note:

- ① Transmission ratio "003" not available with operating mode "S5 cycle mode"
Transmission ratio "050" not available with operating mode "S1 continuous duty"
- ② Driven shaft "C" and "D" not available with operating mode "S1 continuous duty"
- ③ only for motors with liquid cooling
- ④ only for motors without liquid cooling

Permissible combinations

mounting orientation and operating mode	possible transmissions		restricted gear reversal
	single stage	two stage	
CO	3, 4, 5, 7, 10	20	No
MO	4, 5, 7, 10	20, 50	Yes
VO	4, 5, 7, 10	20, 50	Yes

Illustration example: Planetary gearbox