

Design

Curves, diverters, and junctions are available for branching transport of workpiece pallets.

The inlet and outlet of these modules are separately driven via king shafts.

Due to the function, the transport height of the main and secondary sections (inlet and outlet) has a slight difference. This is why curves, diverters, and junctions must always be arranged with an opposite orientation (see the graphic).

Permissible conveyor speed

m_G (kg)	v_N (m/min)
max. 260	12
max. 300	9

m_G = total mass of workpiece pallet

Higher weights available on request



00137413

Arrangement of curves, diverters, and junctions

