

Transportation and nominal speeds v_N

Modular unit	50 Hz		Motor type	60 Hz	
	v_N (m/min)	v [m/min]		v [m/min]	Motor type
AS 2/B-150	18	18.5	734a	18.9	734
	15	15.7	734	13.4	734
	12	11.2	734	13.4	734
	9	8.5	734	10.2	734
	6	5.7	716	6.8	716
AS 2/B-250	18	18.5	824	18.9	824
	15	15.7	824	15.7	824
	12	10.9	824	11.1	814
	9	9.2	814	8.9	734
	6	5.9	734	5.9	716
AS 2/C-100	18	18.5	634	16.6	624
BS 2/C-100	15	13.9	624	13.3	624
CS/C	12	11.1	624	11.1	624
AS 2/R-300	9	9.2	624	8.3	624
BS 2/R-300	6	5.5	624	6.7	624
KU 2/90					
KU 2/180					
BS 2/C-H	18	16.8	744b ¹ /814b ²	15.8	734b
AS 2/C-400	15	13.2	734b	15.8	734b
BS 2/R-H	12	10.4	734b	12.5	734b
AS 2/R-1200	9	8.1	714b	9.8	714b
	6	5.4	716b	6.5	716b
AS 2/C-700	18	16.8	824	17.2	824
AS 2/R-2200	15	14.4	824	14.3	824
	12	11.9	824	12.0	824
	9	8.4	814	8.1	734
	6	5.4	734	6.5	734
AS 2/C-250	18	18.5	734b	17.5	734b
BS 2/C-250	15	14.6	734b	14.5	734b
AS 2/R-700	12	12.0	734b	11.5	734b
BS 2/R-700	9	9.6	734b	9.0	734b
	6	5.9	734b	5.5	714b
BS 2	18	18.0	634	18.0	634
BS 2/M, BS 2/M	15	15.0	634	14.4	634
BS 2/T, BS 2/TE	12	12.0	634	10.8	624
CU 2/90	9	9.0	624	8.7	624
BS 2/K	6	6.0	624	5.4	624
EQ 2/T, EQ 2/TE					
EQ 2/M					
BS 2/130					

v_N = nominal speed

v = conveyor medium speed

¹ For voltage class: B

² For voltage class: A, D

Transportation and nominal speeds v_N

Modular unit	50 Hz		Motor type	60 Hz	
	v_N (m/min)	v [m/min]		v [m/min]	Motor type
HQ 2/U	18	15.8	524	19.0	524
	15	13.2	524	15.8	524
	12	10.6	524	12.7	524
	9	8.3	524	10.0	524
	6	5.7	524	6.8	524
KE 2	18	18.0	524	18.0	524
EQ 2/TR, EQ 2/TR-90	15	15.0	524	14.4	524
	12	12.0	524	10.8	524
	9	9.0	524	9.0	524
HQ 2/S, HQ2/U2	6	6.0	524	5.7	524
HQ 2/C-H	18	18.5	634	16.6	624
	15	13.9	624	13.3	624
	12	11.1	624	11.1	624
	9	9.2	624	8.3	624
	6	5.5	624	6.7	624
HQ 2/U-H	18	16.7	624	20.4	624
	15	16.7	624	15.3	624
	12	12.5	624	10.2	624
	9	8.4	624	7.6	624
	6	6.3	624	6.1	624

v_N = nominal speed
 v = conveyor medium speed

Modular unit	50 Hz			Motor type	60 Hz		Motor type
	v_N (m/min)	v [m/min]	v_T (m/min)		v [m/min]	v_T (m/min)	
BS 2/R-V-1200	18	16.8	42.0	744b ¹ /814b ²	-	-	-
AS 2/R-V-1200	15	13.2	33.0	734b	15.8	39.5	734b
	12	10.4	26.0	734b	12.5	31.3	734b
	9	8.1	20.3	714b	9.8	24.5	714b
	6	5.4	13.5	716b	6.5	16.3	716b
	AS 2/R-V-2200	18	16.8	42.0	824	17.2	43.0
15		14.4	36.0	824	14.3	35.8	824
12		11.9	29.8	824	12.0	30.0	824
9		8.4	21.0	814	8.1	20.3	734
6		5.4	13.5	734	6.5	16.3	734

v_N = nominal speed
 v = conveyor medium speed
 v_T = max. transportation speed

¹ For voltage class: B
² For voltage class: A, D