

## BODAS DI3 Display Interconnection Kits

**USH00029**

Edition: 02.2015



- For 6.5" multifunction color display (series 10, 11) for mobile applications


### Features

- The DI3 interconnection kit is a pre-assembled 12-pin Deutsch Connector and color-coded wire harness.
- The DI3 interconnection kit is wired according to the specifications listed in the DI3 data sheet RE 95270.
- Please Note – there are no 120 ohm (terminating) resistors in the wire harness. These will need to be added as required per application specifications.
- 2 x CAN bus interface 2.0B
- 6' harness with color coded 18 gauge wires
- Kit Order Number: R978730445

### Overview of contents


Connection diagram	2
Connector pinning/display	2
Pin designation	2

Connection Diagram



1) 120 Ω CAN termination resistor necessary for integration in the cable harness

Connector pinning of the display



Pin	Pin designation	Wire color
1	Pin 31 GND	Black
2	CAN2 High	Yellow
3	CAN2 Low	Green
4	CAN1 High	Yellow
5	CAN1 Low	Green
6	Pin 15 (ignition)	Red
7	Pin 58 (light signal)	Red
8	Video input 2	White
9	Video input 1	White
10	GND video input	Black
11	Video camera voltage supply	Red
12	Pin 30 (battery voltage)	Red

**Bosch Rexroth Corp.**  
 Hydraulics  
 8 Southchase Court  
 Fountain Inn, SC 29644-9018  
 U.S.A.  
 Telephone (864) 967-2777  
 Facsimile (864) 967-8900  
 www.boschrexroth-us.com

© All rights reserved Bosch Rexroth Corp. This document, as well as the data, specifications and other information set forth in it, are the exclusive property of Bosch Rexroth Corp. It may not be reproduced or given to third parties with its consent.

The data specified above only serve to describe the product. No statements concerning a certain condition or suitability for a certain application can be derived from our information. The information given does not release the user from the obligation of own judgment and verification. It must be remembered that our products are subject to a natural process of wear and aging.