

# Proportional pressure reducing valve, direct operated, increasing characteristic curve Type DRE05SK



- ▶ Size 5
- ▶ Series 1X
- ▶ Maximum control pressure 30 bar
- ▶ Maximum working pressure 50 bar
- ▶ Maximum flow 30 l/min (at  $\Delta p \leq 7$  bar)

## Features

- ▶ Direct-operated proportional pressure reducing valve for reducing system pressure
- ▶ Cartridge valve
- ▶ Mounting cavity R/DRE 05 TAP
- ▶ Suitable for mobile applications
- ▶ Actuated via proportional solenoid
- ▶ In case of power failure, minimum pressure is set
- ▶ Self-air bleeding pole tube
- ▶ Main application: Gear shifting

## Contents

Ordering details	2
Preferred types	3
Functional description	3
Technical data	4
Characteristic curves	6
Permissible working range	7
Dimensions	8
Available individual components	10
Related documentation	10

## Ordering details

01	02	03	04	05	06	07	08	09	10	11	12	13	14
<b>DRE</b>	<b>05</b>	<b>S</b>	<b>K</b>	<b>1X</b>	/		<b>A</b>		<b>NO</b>		<b>Z</b>	<b>V</b>	<b>*</b>

### Valve type

01	Proportional pressure reducing valve, direct operated, electric actuation	<b>DRE</b>
02	Size 5	<b>05</b>
03	Increasing characteristic curve	<b>S</b>
04	Cartridge valve	<b>K</b>

### Series

05	Series 10 to 19 (unchanged installation and connection dimensions)	<b>1X</b>
----	--	-----------

### Maximum control pressure<sup>1)</sup>

06	20 bar	<b>20</b>
	25 bar	<b>25</b>
	30 bar	<b>30</b>

### Filter

07	Filters in <b>P</b>	<b>P</b>
	Filters in <b>A</b> and <b>P</b>	<b>A</b>

08	Proportional solenoid, switching in oil	<b>A</b>
----	---	----------

### Supply voltage

09	Electronic controls 12 V DC	<b>G12</b>
	Electronic controls 24 V DC	<b>G24</b>

### Manual override

10	<b>Without</b> manual override	<b>NO</b>
----	--------------------------------	-----------

### Electrical connection<sup>2)</sup>

11	Device connector 2-pin DT 04-2P (German)	<b>K40</b>
	Device connector 2-pin, Junior Timer (AMP)	<b>C4</b>

### Connector orientation

12	Radial	<b>Z</b>
----	--------	----------

### Sealing material

13	FKM (fluoroelastomer)	<b>V</b>
----	-----------------------	----------

14	Further details in plain text	<b>*</b>
----	-------------------------------	----------

### Notice

For valve types other than those listed in the data sheet, consultation is required.

1) Other pressure stages on request

2) Plug-in connectors are not included in the scope of delivery and must be ordered separately, see data sheet 08006.

## Preferred types

Type	Material number
DRE 05 SK1X/20PAG12N0K40ZV	R901478532
DRE 05 SK1X/25PAG12N0K40ZV	R901479109
DRE 05 SK1X/30PAG12N0K40ZV	R901479108
DRE 05 SK1X/20PAG24N0K40ZV	R901479096
DRE 05 SK1X/25PAG24N0K40ZV	R901479084
DRE 05 SK1X/30PAG24N0K40ZV	R901479075

Type	Material number
DRE 05 SK1X/20PAG12N0C4ZV	R901479366
DRE 05 SK1X/25PAG12N0C4ZV	R901479371
DRE 05 SK1X/30PAG12N0C4ZV	R901484944
DRE 05 SK1X/20PAG24N0C4ZV	R901479368
DRE 05 SK1X/25PAG24N0C4ZV	R901479372
DRE 05 SK1X/30PAG24N0C4ZV	R901478534

## Functional description

### General

The proportional pressure reducing valve type DRE05SK is a direct operated cartridge valve in 3-way design. It reduces the control pressure (port **A**) proportional to the solenoid current and works largely independently from the inlet pressure (port **P**).

Minimum pressure is set in case of power failure or if the setpoint value is 0. The actuation takes place via a proportional solenoid. The inside of the solenoid is connected with the control pressure port **A** and filled with hydraulic fluid. With these valves, the system pressure can be reduced continuously depending on the electrical setpoint value. The valve is suitable for actuating gears, couplings, pumps and directional valves, as well as for use in proportional pilot controls (particularly in the mobile applications area).

### Basic principle


The valve regulates the pressure in the port **A** proportional to the current on the solenoid.

Version **S** means an increasing characteristic curve, i.e. rising current causes increasing pressure (see characteristic curve on page 6).

The proportional solenoid converts the electric current into mechanical force that acts on the control spool via the anchor. The control spool controls the connection between the main ports.

### Notice

Occurring tank pressure (port **T**) adds up to the control pressure (port **A**).



## Technical data

General				
Weight (approx.)		kg		0.4
Installation position				Any, horizontal preferred
Ambient temperature range		°C		-30 to +120
Salt spray test according to ISO 9227		hr.		720 (NSS test)
Solenoid surface protection				Coating according to DIN 50962-Fe//ZnNi with thick film passivation
Hydraulics				
Maximum control pressure	Port <b>A</b>	$p_A$	bar	20, 25, 30 (others on request)
Maximum inlet pressure	Port <b>P</b>	$p_E$	bar	50 (90 bar including pressure peaks)
Counter-pressure	Port <b>T</b>	$p_T$	bar	Depressurized (maximum 30 bar) Counter-pressure increases set pressure, even when current $I = 0$
Flow ( $\Delta p \leq 7$ bar)	<b>P</b> → <b>A</b>	$q_v$	l/min	30
	<b>A</b> → <b>T</b>	$q_v$	l/min	30
Maximum leakage flow	Port <b>T</b>	$q_L$	ml/min	50 ( $p_E = 50$ bar; $I = 0$ A; $v = 46$ mm <sup>2</sup> /s)
Average pilot flow			ml/min	400 ( $\Delta p = 10$ bar; $I = I_{max}$ ; $v = 46$ mm <sup>2</sup> /s) (max. 600)
Hydraulic fluid				See table on page 5
Hydraulic fluid temperature range		$\vartheta$	°C	-20 to +110 bar (standard) -40 to +120 (on request)
Viscosity range		$\nu$	mm <sup>2</sup> /s	3.7 to 5      limited function 5 to 400      full function 400 to 20000      limited function
Maximum admissible degree of contamination of hydraulic fluid (cleanliness level) according to ISO 4406 (c)				Class 20/18/15 <sup>1)</sup>
Load cycles				10 mil.
Hysteresis (within tolerance range)			bar	≤1.2 (80 % control pressure, PWM 200 Hz)
Repeatability			%	< 3 from maximum control pressure
Step response (depending on system)	0 % → 100 %		ms	≤70
	100 % → 0 %		ms	≤50
Mesh width mesh filter element	Port <b>P</b> ( <b>A</b> optional)		µm	180

1) Cleanliness levels specified for the components must be maintained in the hydraulic systems. Effective filtration prevents malfunctions and simultaneously extends the service life of the components.  
 To select filters, visit [www.boschrexroth.com/filter](http://www.boschrexroth.com/filter).  
 We recommend a filter with a minimum retention rate of  $\beta_{10} \geq 75$ .

Electrical				
Voltage type	DC voltage			
Supply voltage	$U$	V	<b>12</b>	<b>24</b>
Maximum control current	$I_{max}$	mA	1450	690
Coil resistance	Cold value at 20 °C	$\Omega$	4.1	17.5
Duty cycle (ED) <sup>2)</sup>	% See characteristic curve on page 7			
Maximum coil temperature <sup>2)</sup>	°C		185	
Type of protection according to ISO 20653	Connector version "C4"		IP6K5 with installed and locked plug-in connector	
	Connector version "K40"		IP6K7 and IP6K9K with Rexroth plug-in connector, Material no. R901022127	
Connector orientation	As desired (rotatable)			
Electronic controls (separate order)	Type RA... analog amplifier (Data Sheet 95230)			
	Type RC... BODAS controller (data sheets 95204, 95205, 95206)			
Recommended PWM frequency	Hz		250	200
Dither frequency (on request) <sup>3)</sup>				
Design according to VDE 0580				

#### Notice

- ▶ The technical data was determined at a viscosity of  $\nu = 46 \text{ mm}^2/\text{s}$  (HLP46;  $\vartheta_{oil} = 40^\circ\text{C}$ ).
- ▶ Please contact us if the unit will be used outside the specified range of values.
- ▶ For the electrical connection, a protective earth (PE  $\perp$ ) connection is mandatory based on the specification.

#### Hydraulic fluid

Hydraulic fluid	Classification	Suitable sealing materials	Standards	Data sheet
Mineral oils	HL, HLP	FKM	DIN 51524	90220
Biodegradable	insoluble in water	FKM	ISO 15380	90221
	soluble in water	FKM	ISO 15380	

#### Notice

- ▶ Further information and details on using other hydraulic fluids are available in the above data sheets or on request.
- ▶ Restrictions are possible with the technical valve data (temperature, pressure range, service life, maintenance intervals, etc.).
- ▶ The flash point of the hydraulic fluid used must be 40 K above the maximum solenoid surface temperature.
- ▶ **Biodegradable:** When using biodegradable hydraulic fluids that are also zinc-solvent, zinc may accumulate in the fluid.


2) Due to the arising surface temperatures of the solenoid coils, the standards ISO 13732-1 and ISO 4413 must be observed.

3) The dither frequency is to be optimized after the application. The use temperature range is to be observed.


## Characteristic curves

### $\Delta p$ - $I$ -characteristic curve with tolerance band


▼ Control pressure 20 bar, 12 V




▼ Control pressure 20 bar, 24 V




▼ Control pressure 25 bar, 12 V




▼ Control pressure 25 bar, 24 V



▼ Control pressure 30 bar, 12 V




▼ Control pressure 30 bar, 24 V



#### Notice

Characteristic curves measured with HLP46,  $\vartheta_{oil} = 40 \pm 5 \text{ } ^\circ\text{C}$ .


**$\Delta p$ - $q_v$ -flow characteristic curve**



**Permissible working range**

**Minimum terminal voltage on the coil, relative duty cycle and permissible working range depending on the ambient temperature**


▼ **12 V** ( $R_{nom} = 4.1 \Omega$ ;  $\vartheta_{coil max} = 185 \text{ }^\circ\text{C}$ ;  $I_{nom} = 1.45 \text{ A}$ )



**Notice**


The characteristic curves were determined for coils with valve for medium test block size (80 x 80 x 80 mm), w/o flow in still air. Depending on installation conditions (block size, flow, air circulation, etc.) heat dissipation may be better. This increases the range of applications. In specific instances, unfavorable conditions may limit the range of applications.

▼ **24 V** ( $R_{nom} = 17.5 \Omega$ ;  $\vartheta_{coil max} = 185 \text{ }^\circ\text{C}$ ;  $I_{nom} = 0.69 \text{ A}$ )




## Dimensions

### ▼ DRE05SK, Design "C4"



### ▼ DRE05SK, Design "K40"



- 1 Plug-in connector for device connector "C4"  
(separate order, see Data Sheet 08006)
- 2 Plug-in connector for device connector "K40"  
(separate order, see Data Sheet 08006)
- 3 Recommended mounting bolts (separate order):  
2 pieces M6×1-12-8.8 according to ISO 4762  
tightening torque:  
Aluminum:  $M_A = 6^{+2}$  Nm  
GGG40:  $M_A = 6^{+2}$  Nm  
steel:  $M_A = 6^{+2}$  Nm
- 4 Filter on port A optional



