

## Stop gate VE 2/D-220



- ▶ Pneumatic stop gate
- ▶ Economical plastic version with
- ▶ double piston damper
- ▶ Continuously adjustable damping
- ▶ Optimal damping for total WT weights of up to 220 kg
- ▶ Damping path 27.5 mm
- ▶ Linear lowering stroke
- ▶ Short installation dimension
- ▶ Can be combined with WT 2 and WT 2/F
- ▶ Installation of a clamping holder with sensor allows for querying the upper and lower positions

Dampened stopping of the first accumulating workpiece pallet. The stop gate stops one or more accumulating workpiece pallets at the defined workpiece pallet stop surface. When the pressure is released, the stop gate is

held in the lock position by a spring and the workpiece pallet is stopped. Mounted inside the tracks, directly on the conveyor section.

### Required accessories

- ▶ Return stop VE 2/RS
- ▶ Clamping holder (3842545974)
- ▶ Sensor M12×1 (3842549814)

### Scope of delivery

- ▶ Incl. fastening material for installation on conveyor section ST2/...
- ▶ Pneumatic elements

### Condition on delivery

- ▶ Assembled

### Ordering information

Product description	Material number
Stop gate VE 2/D-220	3842567562

